### **Super-Luminescent Light Emitting Diode (SLD)**

**TO CAN Packaged Devices** 



#### **Features**

- High power and broad band
- Low coherence length
- Uncooled & Cooled TO package
- Monitor PD is an option


### **Applications**

- Medical diagnostic systems
- Optical Fiber sensor systems
- Illumination


### **IPSDT0803 SLD TO CAN Specifications (Tcase=25°C)**


Parameter	Min.	Тур.	Max.	Unit	Test Condition
Central Wavelength	800	820	840	nm	
3 dB Bandwidth	20	25	-	nm	
Output Power	5	8	-	mW	Flat Window Output
Operating Current	-	140	200	mA	
Forward Voltage	-	-	-	V	
Spectral Ripple	-	0.1	0.5	dB	
Beam Spread Angle:	-	-	-		
- Parallel	-	10	25	degree	
- Vertical	-	38	45	degree	

Detailed Information about operation/storage temperature available upon request: Contact <a href="mailto:sales@inphenix.com">sales@inphenix.com</a> for more details




Pin#	Connection
1	SLD Anode
2	SLD Cathode, PD
_	Cathode and Case
3	PD Anode






φ9 mm TO-CAN (TO5/TO9/TO39)

All information contained herein is believed to be accurate and is subject to change without notification. No responsibility is assumed. Please contact InPhenix for more information. InPhenix and the InPhenix logo are trademarks of InPhenix Inc. All rights are reserved.



Pin#	Connection	
1	PD Anode	
2	SLD Cathode, PD Cathode and Case	
3	SLD Anode	
4		

<b>Pigtail Information</b>					
Connector	TBD				
Fiber	SMF				
Fiber Length	0.5 m				



φ5.6 mm Pigtailed Coaxial Device (TO56 Header)

#### **Part Numbering System**

Model-					
IPSDT0701: 750nm SLD TO CAN					
IPSDT080X: 820nm SLD TO CAN					
IPSDT090X: 900nm SLD TO CAN					
IPSDT13XX: 1310nm SLD TO CAN					
IPSDT150X: 1550nm SLD TO CAN					
Davidson .					
Package-					
7: TO 56					
8: TO 8					
9: TO 9					
Fiber Type:					
0: No Fiber 1: Single Mode 5: Ball Lens					
6: Flat Glass 7: Aspheric Lens					
Jacket Type:					
0: No Jacket					
1: 900 μm					
2: 250 µm tight buffer					
Connector Type:					
0: No Connectors					

- 3: FC/APC
- 4: FC/UPC
- 7: SC/APC
- 8: SC/UPC

#### **Back Facet Monitor:**

Available upon request

Example: IPSDT0801-9700: 820nm SLD, TO9 package with Aspheric lens.

### **Corporate Office**

250 North Mines Rd Livermore, CA 94551 Tel: 925.606.8809 Fax: 925.606.8810 www.inphenix.com sales@inphenix.com